



HXT045HK

**Motor Operator P250 200-220VAC/DC with Auto-Reset +key**

**Technical properties**

**Architecture**

Type of order motor drive

**Main electrical features**

Type of supply voltage AC/DC

**Voltage**

DC control voltage 200 / 220 V

Command voltage AC 200 / 220 V

**Electric current**

Inrush current OFF-RESET 200-220V AC - 6.6A ; 200-220V DC - 5.9A

Inrush current ON 200-220V AC - 6.6A ; 200-220V DC - 5.9A

Operating current OFF-RESET 200-220V AC - 3.6A ; 200-220V DC - 4.2A

Operating current ON 200-220V AC - 3.6A ; 200-220V DC - 4.2A

**Frequency**

Frequency 50 to 60 Hz

**Standards**

European directive RoHS voluntary compliance

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free No

**Use conditions**

Altitude 2000 m