



HXT045HK

Motor Operator P250 200-220VAC/DC with Auto-Reset +key

Technical properties

Architecture

Type of order motor drive

Main electrical features

Type of supply voltage AC/DC

Voltage

DC control voltage 200 / 220 V

Command voltage AC 200 / 220 V

Electric current

Inrush current OFF-RESET 200-220V AC - 6.6A ; 200-220V DC - 5.9A

Inrush current ON 200-220V AC - 6.6A ; 200-220V DC - 5.9A

Operating current OFF-RESET 200-220V AC - 3.6A ; 200-220V DC - 4.2A

Operating current ON 200-220V AC - 3.6A ; 200-220V DC - 4.2A

Frequency

Frequency 50 to 60 Hz

Standards

European directive RoHS voluntary compliance

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Use conditions

Altitude 2000 m