



HXT047HK

## Motor Operator P250 200-220VAC/DC without Auto-Reset +key

### Technical properties

#### Architecture

Type of order motor drive

#### Main electrical features

Type of supply voltage AC/DC

#### Voltage

DC control voltage 200 / 220 V

Command voltage AC 200 / 220 V

#### Electric current

Inrush current OFF-RESET 200-220V AC - 6.6A ; 200-220V DC - 5.9A

Inrush current ON 200-220V AC - 6.6A ; 200-220V DC - 5.9A

Operating current OFF-RESET 200-220V AC - 3.6A ; 200-220V DC - 4.2A

Operating current ON 200-220V AC - 3.6A ; 200-220V DC - 4.2A

#### Frequency

Frequency 50 to 60 Hz

#### Standards

European directive RoHS voluntary compliance

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

#### Use conditions

Altitude 2000 m