



HXT048H

Motor Operator P250 48VDC with Auto-Reset

Technical properties

Architecture

Type of order	motor drive
---------------	-------------

Main electrical features

Type of supply voltage	DC
------------------------	----

Voltage

DC control voltage	48 V
--------------------	------

Command voltage AC	0 V
--------------------	-----

Electric current

Inrush current OFF-RESET	48V DC - 17A
--------------------------	--------------

Inrush current ON	48V DC - 12A
-------------------	--------------

Operating current OFF-RESET	48V DC - 12A
-----------------------------	--------------

Operating current ON	48V DC - 12A
----------------------	--------------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Altitude	2000 m
----------	--------