



HYB001H

## Collar terminal x250 Al/Cu 3P

### Technical properties

#### Architecture

Number of poles	3 P
-----------------	-----

#### Electric current

Rated current	250 A
---------------	-------

#### Installation, mounting

Tightening torque	25Nm
-------------------	------

#### Connection

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
---	-------------------------

Conductor cross-section	35...185 mm <sup>2</sup>
-------------------------	--------------------------

#### Cable

Cable Material	Cu / Al
----------------	---------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

#### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
--	---

Altitude	2000 m
----------	--------