



HYD006H

Collar terminal h400/h630 Al 4P 1x 95-240mm²

Technical properties

Architecture

Number of poles 4 P

Electric current

Rated current 630 A

Installation, mounting

Tightening torque 25Nm

Connection

Connection cross-sect. flexible conductor 35 / 240mm²

Connection cross-sect. rigid cable 35 / 240mm²

Cable

Cable Material Cu / Al

Standards

European directive WEEE concerned

Safety

Protection index IP IP4X

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m