



HYD008H

**Collar terminal h400/h630 Al 4P 2x 95-240mm<sup>2</sup>**

**Technical properties**

**Architecture**

Number of poles 4 P

**Electric current**

Rated current 630 A

**Installation, mounting**

Tightening torque 25Nm

**Connection**

Connection cross-sect. flexible conductor 35 / 240mm<sup>2</sup>

Connection cross-sect. rigid cable 2x 35/240 mm<sup>2</sup>

**Cable**

Cable Material Cu / Al

**Standards**

European directive WEEE concerned

**Safety**

Protection index IP IP4X

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m