



HYE007H

Collar terminal h800/h1000 Al 3P 4x 95-240mm²

Technical properties

Architecture

Number of poles 3 P

Electric current

Rated current 800 A

Installation, mounting

Tightening torque 25Nm

Connection

Connection cross-sect. flexible conductor 35 / 240mm²

Connection cross-sect. rigid cable 4x 35/240 mm²

Conductor cross-section 95...240 mm²

Cable

Cable Material Cu / Al

Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2 3

Altitude 2000 m