



HYW002H

Cage terminal x630/P630 Cu/Al 4P 1x 35-300mm²

Technical properties

Architecture

Number of poles	4 P
Type of pole	4 P

Electric current

Rated current	630 A
---------------	-------

Power

Total power loss under IN	211.2 W
Power loss per pole at In	70.4 W

Installation, mounting

Tightening torque	25Nm
-------------------	------

Connection

Conductor cross-section	35...300 mm ²
-------------------------	--------------------------

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes