



HYW008H

**Cage terminal x630/P630 Cu/Al 4P 2x 35-300mm<sup>2</sup>**

**Technical properties**

**Architecture**

Number of poles	4 P
Type of pole	4 P

**Electric current**

Rated current	630 A
---------------	-------

**Power**

Total power loss under I <sub>N</sub>	321.49 W
Power loss per pole at I <sub>N</sub>	107.16 W

**Installation, mounting**

Tightening torque	25Nm
-------------------	------

**Connection**

Conductor cross-section	2 x 35...300 mm <sup>2</sup>
-------------------------	------------------------------

**Standards**

European directive RoHs	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes