



HZC311

Auxiliary contact 1C+1O LBS 20-160A

Technical properties

Main electrical features

Frequency	50 Hz
-----------	-------

Connection

Connection cross-sect. flexible conductor	2,5mm ²
Connection cross-sect. rigid cable	2,5mm ²
Type of connection	with screw

Equipment

Number of auxiliary contacts as normally closed contact	1
Number of auxiliary contacts as normally open contact	1
Number of auxiliary contacts as change-over contact	0

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-20...70 °C
Storage/transport temperature	-40...65 °C