



HZI910

## Remote interface

## Technical properties

### Dimensions

Height of installed product	96 mm
Width of installed product	96 mm

### Power

Total power loss under IN	0 W
Power loss per pole at In	0 W

### Installation, mounting

Mounting type	flush-mounted
---------------	---------------

### Connection

Type of connector connection 1	RJ45 8(8)
--------------------------------	-----------

### Cable

Line length	3 m
-------------	-----

### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

### Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-10...55 °C