



HZI910

## Remote interface

## Technical properties

### Dimensions

|                             |       |
|-----------------------------|-------|
| Height of installed product | 96 mm |
| Width of installed product  | 96 mm |

### Power

|                           |     |
|---------------------------|-----|
| Total power loss under IN | 0 W |
| Power loss per pole at In | 0 W |

### Installation, mounting

|               |               |
|---------------|---------------|
| Mounting type | flush-mounted |
|---------------|---------------|

### Connection

|                                |           |
|--------------------------------|-----------|
| Type of connector connection 1 | RJ45 8(8) |
|--------------------------------|-----------|

### Cable

|             |     |
|-------------|-----|
| Line length | 3 m |
|-------------|-----|

### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | No  |

### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10...55 °C |
| Storage/transport temperature | -10...55 °C |