



HZI911

Remote interface

Technical properties

Dimensions

Height of installed product	96 mm
Width of installed product	96 mm

Power

Total power loss under IN	0 W
Power loss per pole at In	0 W

Installation, mounting

Mounting type	flush-mounted
---------------	---------------

Connection

Type of connector connection 1	RJ45 8(8)
--------------------------------	-----------

Cable

Line length	3 m
-------------	-----

Equipment

Type of display	LCD
-----------------	-----

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-10...55 °C
Storage/transport temperature	-10...55 °C