



K018

Main line branch terminal, universal, 1 pole, 1x25mm²- 4x16 mm²

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth of installed product	40 mm
----------------------------	-------

Height of installed product	55 mm
-----------------------------	-------

Width of installed product	40 mm
----------------------------	-------

Connection

Type of connection	screw
--------------------	-------

Equipment

Number of outputs	2
-------------------	---

Number of inputs	1
------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----