



K023

Main line branch terminal, universal, 2 pole, 1x25mm² - 4x16 mm² per pole

Technical properties

Architecture

Number of poles	2 P
Fixing mode	Clamping and screwable

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth of installed product	35 mm
Height of installed product	55 mm
Width of installed product	65 mm

Connection

Connection cross-sect. rigid cable	25mm ²
Type of connection	screw

Settings

terminal type	Branch terminal
---------------	-----------------

Equipment

Number of outputs	4
Number of inputs	3

Standards

European directive WEEE	concerned
-------------------------	-----------