



K89000

**Mini DIN rail terminal, 2,5mm<sup>2</sup>, stackable, 24A/300V, blue, without mounting base**

#### Technical properties

##### Architecture

Fixing mode	pluggable
-------------	-----------

##### Electric current

Rated current	20 A
---------------	------

##### Dimensions

Depth of installed product	28 mm
Height of installed product	18 mm
Width of installed product	6 mm

##### Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

##### Connection

Connection cross-sect. flexible conductor	0,3 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,14 / 2,5mm <sup>2</sup>
Terminal cross-section	1.5 mm <sup>2</sup>
Type of connection	quick connect

##### Settings

terminal type	Terminal block
---------------	----------------

##### Safety

REACH conform	Yes
RoHS conform	Yes