



K89100

Mini DIN rail terminal, 2,5mm², stackable, 24A/300V, gray, without mounting base

Technical properties

Architecture

Fixing mode	pluggable
-------------	-----------

Electric current

Rated current	20 A
---------------	------

Dimensions

Depth of installed product	28 mm
Height of installed product	18 mm
Width of installed product	6 mm

Power

Total power loss under IN	0 W
Dissipated energy in cable	0 W

Materials

Colour	stone grey
Colour	dark grey
Material	Polyamid (PA)

Connection

Terminal cross-section	1.5 mm ²
Type of connection	quick connect

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes