



K89200

Mini DIN rail terminal, 2,5mm², stackable, 24A/300V, green, without mounting base

Technical properties

Architecture

Fixing mode pluggable

Electric current

Rated current 20 A

Dimensions

Depth of installed product 28 mm

Height of installed product 18 mm

Width of installed product 6 mm

Power

Total power loss under IN 0 W

Dissipated energy in cable 0 W

Connection

Connection cross-sect. flexible conductor 0,3 / 2,5mm²

Connection cross-sect. rigid cable 0,14 / 2,5mm²

Terminal cross-section 1.5 mm²

Type of connection quick connect

Settings

terminal type Terminal block

Safety

REACH conform Yes

RoHS conform Yes