



KB190C

Insulated busbar 1P 100A prong 20mm² 24M

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Configuration

Number of modules	24
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	100 A
---------------	-------

Dimensions

Length	420 mm
Pitch	17.8 mm
Fixation distance in module steps	1

Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Suitable for product with neutral busbar	No
--	----

Equipment

Number of appliances to build in	24
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

