



KB190C

## Insulated busbar 1P 100A prong 20mm<sup>2</sup> 24M

### Technical properties

#### Architecture

Number of poles	1 P
-----------------	-----

#### Configuration

Number of modules	24
-------------------	----

#### Compatibility

Intended for the compatible references	Modular devices
--	-----------------

#### Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

#### Voltage

Max operating voltage	230 V
Rated impulse withstand voltage	4 kV

#### Electric current

Rated current	100 A
---------------	-------

#### Dimensions

Length	420 mm
Pitch	17.8 mm
Fixation distance in module steps	1

#### Power supply

Number of phases for the power supply	1 phase
---------------------------------------	---------

#### Materials

Colour	stone grey
--------	------------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Suitable for product with neutral busbar	No
Type of connection	with screw

#### Equipment

Number of appliances to build in	24
----------------------------------	----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
<b>Use conditions</b>	
Insulated	Yes