



KB280B

Insulated busbar 2P 80A prong 16mm² 57M

Technical properties

Architecture

Number of poles	2 P
Type of pole	2 P

Configuration

Number of modules	57
-------------------	----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	2

Power supply

Number of phases for the power supply	2 phases
---------------------------------------	----------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	16mm ²
Suitable for product with neutral busbar	Yes

Equipment

Number of appliances to build in	28
----------------------------------	----

Standards

Use conditions

Insulated

Yes