



KB280B

**Insulated busbar 2P 80A prong 16mm<sup>2</sup> 57M**

**Technical properties**

**Architecture**

Number of poles 2 P

**Configuration**

Number of modules 57

**Compatibility**

Intended for the compatible references Modular devices

**Main electrical features**

Rated operational voltage Ue 230 / 400 V

**Voltage**

Max operating voltage 400 V

Rated impulse withstand voltage 4 kV

**Electric current**

Rated current 80 A

**Dimensions**

Length 1000 mm

Pitch 17.8 mm

Fixation distance in module steps 2

**Power supply**

Number of phases for the power supply 2 phases

**Installation, mounting**

Suitable to a device with an auxiliary No

**Connection**

Connection cross-sect. rigid cable 16mm<sup>2</sup>

Suitable for product with neutral busbar Yes

Connector type busbar prong

**Equipment**

Number of appliances to build in 28

**Standards**

European directive WEEE concerned

**Safety**

REACH conform	No
RoHS conform	Yes
<b>Use conditions</b>	
Insulated	Yes