



Insulated busbar 1P 100A fork 20mm² 57M

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Compatibility

Intended for the compatible references	Modular devices
--	-----------------

Main electrical features

Rated operational voltage Ue	415 V
------------------------------	-------

Voltage

Max operating voltage	230 V
-----------------------	-------

Electric current

Rated current	100 A
---------------	-------

Dimensions

Length	1000 mm
--------	---------

Pitch	17.8 mm
-------	---------

Fixation distance in module steps	1
-----------------------------------	---

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Suitable for product with neutral busbar	No
--	----

Type of connection	with screw
--------------------	------------

Equipment

Number of appliances to build in	57
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Use conditions

Insulated	Yes
-----------	-----

KD190B