



KD302M

Insulated busbar for 2 motor starters 3P 63A fork 10mm²

Technical properties

Architecture

Number of poles	3 P
Type of pole	3 P

Compatibility

Intended for the compatible references	Motor starter
--	---------------

Main electrical features

Rated operational voltage U _e	230 / 400 V
--	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	88 mm
Pitch	17.8 mm

Installation, mounting

Suitable to a device with an auxiliary	Yes
--	-----

Connection

Connection cross-sect. rigid cable	10mm ²
Suitable for product with neutral busbar	No
Connector type	busbar fork
Type of connection	with screw

Safety

REACH conform	No
RoHS conform	Yes

Use conditions

Operating temperature	-25...55 °C
Storage/transport temperature	-25...80 °C
Insulated	Yes