



KD302M

**Insulated busbar for 2 motor starters 3P 63A fork 10mm<sup>2</sup>**

**Technical properties**

**Architecture**

Number of poles	3 P
Type of pole	3 P

**Compatibility**

Intended for the compatible references	Motor starter
--	---------------

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
-----------------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Length	88 mm
Pitch	17.8 mm

**Materials**

Colour	stone grey
--------	------------

**Installation, mounting**

Suitable to a device with an auxiliary	Yes
--	-----

**Connection**

Connection cross-sect. rigid cable	10mm <sup>2</sup>
Suitable for product with neutral busbar	No
Connector type	busbar fork
Type of connection	with screw

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-25...55 °C
Storage/transport temperature	-25...80 °C
Insulated	Yes