



KD304M

Insulated busbar for 4 motor starters 3P 63A fork 10mm²

Technical properties

Architecture

Number of poles	3 P
-----------------	-----

Compatibility

Intended for the compatible references	Motor starter
--	---------------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	176 mm
--------	--------

Pitch	17.8 mm
-------	---------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	Yes
--	-----

Connection

Suitable for product with neutral busbar	No
--	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-25...55 °C
-----------------------	-------------

Storage/transport temperature	-25...80 °C
-------------------------------	-------------

Insulated	Yes
-----------	-----