



KDN263B

Insulated busbar 2P 63A fork 10mm² 57M

Technical properties

Architecture

Number of poles	2 P
Type of pole	2 P

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	2

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Suitable for product with neutral busbar	Yes
--	-----

Equipment

Number of appliances to build in	28
----------------------------------	----

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Insulated	Yes
-----------	-----