



KDN363B

Insulated busbar 3P 63A fork 10mm² 57M

Technical properties

Architecture

Number of poles 3 P

Compatibility

Intended for the compatible references Modular devices

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Electric current

Rated current 63 A

Dimensions

Length 1000 mm

Pitch 17.8 mm

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 10mm²

Suitable for product with neutral busbar No

Connector type busbar fork

Equipment

Number of connections 57 C

Standards

European directive WEEE concerned

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Insulated Yes