



KDN451E

Insulated busbar 3x(P+N) 80A fork 16mm² 57M

Technical properties

Architecture

Number of poles	4 P
Type of pole	3P+N

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	1000 mm
Pitch	17.8 mm

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	16mm ²
Suitable for product with neutral busbar	Yes
Connector type	busbar fork
Type of connection	with screw / quick connect

Equipment

Number of appliances to build in	54
----------------------------------	----

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Insulated	Yes
-----------	-----