



KDN451E

Insulated busbar 3x(P+N) 80A fork 16mm² 57M

Technical properties

Architecture

Number of poles 4 P

Main electrical features

Rated operational voltage Ue 230 / 400 V

Voltage

Max operating voltage 400 V

Electric current

Rated current 80 A

Dimensions

Length 1000 mm

Pitch 17.8 mm

Materials

Colour stone grey

Installation, mounting

Suitable to a device with an auxiliary No

Connection

Connection cross-sect. rigid cable 16mm²

Suitable for product with neutral busbar Yes

Equipment

Number of appliances to build in 54

Standards

European directive WEEE concerned

Use conditions

Insulated Yes