



KDN463B

**Insulated busbar 4P 63A fork 10mm<sup>2</sup> 57M**

**Technical properties**

**Architecture**

Number of poles	4 P
Type of pole	4 P

**Main electrical features**

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

**Voltage**

Max operating voltage	400 V
-----------------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	4

**Materials**

Colour	stone grey
--------	------------

**Installation, mounting**

Suitable to a device with an auxiliary	No
--	----

**Connection**

Suitable for product with neutral busbar	Yes
--	-----

**Equipment**

Number of appliances to build in	14
----------------------------------	----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

Insulated	Yes
-----------	-----