



KDN463B

## Insulated busbar 4P 63A fork 10mm<sup>2</sup> 57M

### Technical properties

#### Architecture

Number of poles	4 P
Type of pole	4 P

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

#### Voltage

Max operating voltage	400 V
-----------------------	-------

#### Electric current

Rated current	63 A
---------------	------

#### Dimensions

Length	1000 mm
Pitch	17.8 mm
Fixation distance in module steps	4

#### Materials

Colour	stone grey
--------	------------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Suitable for product with neutral busbar	Yes
--	-----

#### Equipment

Number of appliances to build in	14
----------------------------------	----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

#### Use conditions

Insulated	Yes
-----------	-----