



KF30M

Cable terminal for motor starter 3P 63A fork 10mm²

Technical properties

Architecture

Type of pole 3 P

Configuration

Number of modules 2.5

Voltage

Max operating voltage 400 V

Electric current

Rated current 63 A

Materials

Material Mixed materials

Connection

Connection cross-sect. rigid cable 10mm²

Accessories included

Type of accessory Connection clamp

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -25...55 °C

Altitude 2000 m

Storage/transport temperature -25...80 °C