



KF30M

Cable terminal for motor starter 3P 63A fork 10mm²

Technical properties

Architecture

Type of pole	3 P
--------------	-----

Configuration

Number of modules	2.5
-------------------	-----

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	63 A
---------------	------

Connection

Connection cross-sect. rigid cable	10mm ²
------------------------------------	-------------------

Safety

REACH conform	No
RoHS conform	Yes

Use conditions

Operating temperature	-25...55 °C
Altitude	2000 m
Storage/transport temperature	-25...80 °C