



KF82A

**Cable terminal 1P prong 2 cables 16mm<sup>2</sup>**

**Technical properties**

**Architecture**

Number of poles 1 P

**Functions**

Suitable for fine strand conductors No

Suitable for fine strand conductors without cable end sleeve No

Suitable for extra fine-strand conductors No

Suitable for extra fine-strand conductors without cable end sleeve No

**Electric current**

Rated current 63 A

**Connection**

Connection cross-sect. flexible conductor 2x10mm<sup>2</sup>

Connection cross-sect. rigid cable 2x16mm<sup>2</sup>

Terminal cross-section 16 mm<sup>2</sup>

Type of connection with screw

**Equipment**

Number of outputs 1

Number of inputs 1

**Safety**

REACH conform No

RoHS conform Yes

Halogen free Yes