



KF83A

**Connection terminal 1P prong 1x35mm<sup>2</sup>**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	1 P

**Functions**

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

**Voltage**

Max operating voltage	500 V
-----------------------	-------

**Electric current**

Rated current	100 A
---------------	-------

**Connection**

Connection cross-sect. flexible conductor	25mm <sup>2</sup>
Connection cross-sect. rigid cable	35mm <sup>2</sup>
Terminal cross-section	35 mm <sup>2</sup>
Type of connection	with screw

**Equipment**

Number of outputs	0
Number of inputs	1

**Safety**

REACH conform	No
RoHS conform	Yes