



KF83B

Connection terminal 1P prong 2x25mm²

Technical properties

Architecture

Type of pole	1 P
Fixing mode	Screwed

Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

Voltage

Max operating voltage	500 V
-----------------------	-------

Electric current

Rated current	100 A
---------------	-------

Materials

Material	Mixed materials
----------	-----------------

Connection

Connection cross-sect. flexible conductor	2x16mm ²
Connection cross-sect. rigid cable	2x25mm ²
Terminal cross-section	25 mm ²
Type of connection	with screw

Accessories included

Type of accessory	Connection clamp
-------------------	------------------

Equipment

Number of outputs	1
Number of inputs	1

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes