



KF83C

Extended connection terminal 1P prong 1x35mm²

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

Voltage

Max operating voltage	500 V
-----------------------	-------

Electric current

Rated current	100 A
---------------	-------

Connection

Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²
Terminal cross-section	35 mm ²
Type of connection	with screw

Equipment

Number of outputs	0
Number of inputs	1

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-5...60 °C
Storage/transport temperature	-25...80 °C