



KF83D

Connection terminal 1P prong 1x35mm²

Technical properties

Architecture

Number of poles	1 P
Fixing mode	Screwed

Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

Voltage

Max operating voltage	500 V
-----------------------	-------

Electric current

Rated current	100 A
---------------	-------

Materials

Material	Mixed materials
----------	-----------------

Connection

Terminal cross-section	35 mm ²
Type of connection	with screw

Accessories included

Type of accessory	Connection clamp
-------------------	------------------

Equipment

Number of outputs	0
Number of inputs	1

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-5...60 °C
Storage/transport temperature	-25...80 °C