



KF84A

Cable terminal 1P fork 1 cable 25mm²

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

Electric current

Rated current	80 A
---------------	------

Connection

Connection cross-sect. flexible conductor	16mm ²
Connection cross-sect. rigid cable	25mm ²
Terminal cross-section	25 mm ²
Type of connection	with screw

Equipment

Number of outputs	0
Number of inputs	1

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	Yes