



KJ100A

**Brass busbar terminal 100A, 4pole, 2x 2,5-25<sup>2</sup> / 5x 1,5-16<sup>2</sup> per pole**

## Technical properties

### Architecture

Number of poles	4 P
-----------------	-----

### Configuration

Number of modules	4
-------------------	---

### Electric current

Rated current	100 A
---------------	-------

### Dimensions

Depth of installed product	44 mm
Height of installed product	97 mm
Width of installed product	71 mm

### Materials

Brass weight of the product	130 g
-----------------------------	-------

### Installation, mounting

Tightening torque	2Nm
-------------------	-----

### Connection

Connection cross-sect. flexible conductor	1,5 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 25mm <sup>2</sup>
Conductor cross-section (flexible), with wire end sleeve	1.5...16 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...25 mm <sup>2</sup>

### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	Yes