



KJ100A

**Brass busbar terminal 100A, 4pole, 2x 2,5-25<sup>2</sup> / 5x 1,5-16<sup>2</sup> per pole**

**Technical properties**

**Architecture**

Number of poles 4 P

**Configuration**

Number of modules 4

**Electric current**

Rated current 100 A

**Dimensions**

Depth of installed product 44 mm

Height of installed product 97 mm

Width of installed product 71 mm

**Materials**

Brass weight of the product 130 g

**Installation, mounting**

Tightening torque 2Nm

**Connection**

Connection cross-sect. flexible conductor 1,5 / 16mm<sup>2</sup>

Connection cross-sect. rigid cable 1,5 / 25mm<sup>2</sup>

Conductor cross-section (flexible), with wire end sleeve 1.5...16 mm<sup>2</sup>

Conductor cross-section (rigid) 1.5...25 mm<sup>2</sup>

**Safety**

REACH conform No

RoHS conform Yes

Halogen free Yes