



KJ125B

Brass busbar terminal 125A, 4pole, 1x 10-35² / 3x 6-35² / 11x 1,5-16² per pole

Technical properties

Architecture

Number of poles	4 P
-----------------	-----

Configuration

Number of modules	10
-------------------	----

Electric current

Rated current	125 A
---------------	-------

Dimensions

Depth	64 mm
Depth of installed product	64 mm
Height of installed product	96 mm
Width of installed product	170 mm

Materials

Brass weight of the product	260 g
-----------------------------	-------

Installation, mounting

Tightening torque	2,5Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1,5 / 25mm ²
Connection cross-sect. rigid cable	1,5 / 35mm ²

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	Yes