



KJ125B

Brass busbar terminal 125A, 4pole, 1x 10-35² / 3x 6-35² / 11x 1,5-16² per pole

Technical properties

Architecture

Number of poles 4 P

Configuration

Number of modules 10

Electric current

Rated current 125 A

Dimensions

Depth 64 mm

Depth of installed product 64 mm

Height of installed product 96 mm

Width of installed product 170 mm

Materials

Brass weight of the product 260 g

Installation, mounting

Tightening torque 2,5Nm

Connection

Connection cross-sect. flexible conductor 1,5 / 25mm²

Connection cross-sect. rigid cable 1,5 / 35mm²

Safety

REACH conform No

RoHS conform Yes

Halogen free Yes