



KJ160A

**Brass busbar terminal 160A, 4pole, 1x 25-70<sup>2</sup> / 3x 10-35<sup>2</sup> / 8x 2,5-25<sup>2</sup> per pole**

**Technical properties**

**Architecture**

Number of poles 4 P

**Configuration**

Number of modules 9

**Electric current**

Rated current 160 A

**Dimensions**

Depth of installed product 44 mm

Height of installed product 96 mm

Width of installed product 162 mm

**Installation, mounting**

Tightening torque 5Nm

**Connection**

Connection cross-sect. flexible conductor 50mm<sup>2</sup>

Connection cross-sect. rigid cable 2,5 / 70mm<sup>2</sup>

**Standards**

European directive WEEE concerned

**Safety**

REACH conform No

RoHS conform Yes

Halogen free Yes