



KJ160A

**Brass busbar terminal 160A, 4pole, 1x 25-70<sup>2</sup> / 3x 10-35<sup>2</sup> / 8x 2,5-25<sup>2</sup> per pole**

### Technical properties

#### Architecture

Number of poles	4 P
-----------------	-----

#### Configuration

Number of modules	9
-------------------	---

#### Electric current

Rated current	160 A
---------------	-------

#### Dimensions

Depth of installed product	44 mm
----------------------------	-------

Height of installed product	96 mm
-----------------------------	-------

Width of installed product	162 mm
----------------------------	--------

#### Installation, mounting

Tightening torque	5Nm
-------------------	-----

#### Connection

Connection cross-sect. flexible conductor	50mm <sup>2</sup>
-------------------------------------------	-------------------

Connection cross-sect. rigid cable	2,5 / 70mm <sup>2</sup>
------------------------------------	-------------------------

#### Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----