



KM10N

Brass terminal, 8x10mm² -2x16mm²(double drive),with mounting base, Color: blue

Technical properties

Architecture

| | |
|-----------------|------------------------|
| Number of poles | 1 P |
| Fixing mode | Clamping and screwable |

Electric current

| | |
|---------------|------|
| Rated current | 60 A |
|---------------|------|

Dimensions

| | |
|----------------------------|-------|
| Length | 69 mm |
| Width of installed product | 5 mm |

Settings

| | |
|---------------|------------------|
| terminal type | Brass terminal N |
|---------------|------------------|

Equipment

| | |
|-------------------|---|
| Number of outputs | 9 |
| Number of inputs | 1 |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Safety

| | |
|---------------|-----|
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |