



KM13N

**Brass terminal, 7x10mm<sup>2</sup> 6x16mm<sup>2</sup>,with mounting base, Color: blue**

**Technical properties**

**Architecture**

Number of poles	1 P
Fixing mode	Clamping and screwable

**Functions**

Suitable for fine strand conductors	Yes
Suitable for fine strand conductors without cable end sleeve	Yes
Suitable for extra fine-strand conductors	Yes
Suitable for extra fine-strand conductors without cable end sleeve	Yes

**Electric current**

Rated current	60 A
---------------	------

**Dimensions**

Length	85 mm
Width of installed product	5 mm

**Settings**

terminal type	Brass terminal N
---------------	------------------

**Equipment**

Number of outputs	12
Number of inputs	1

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No