



KM25N

**Brass terminal, 1x25mm<sup>2</sup> 13x10mm<sup>2</sup> 11x16mm<sup>2</sup>,with mounting base, Color: blue**

#### Technical properties

##### Architecture

Number of poles	1 P
Fixing mode	Clamping and screwable

##### Electric current

Rated current	60 A
---------------	------

##### Dimensions

Length	169 mm
Width of installed product	5 mm

##### Settings

terminal type	Brass terminal N
---------------	------------------

##### Equipment

Number of outputs	24
Number of inputs	1

##### Standards

European directive WEEE	concerned
-------------------------	-----------

##### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No